



AMH55

Hardness Testing Systems



LECO
EMPOWERING RESULTS

AMH55

Hardness Testing Systems

Maximize your productivity and easily measure impressions on various surface conditions for a wide number of applications with LECO's AMH55. The AMH55 introduces LECO's innovative Cornerstone® brand software to our hardness testing platforms, for increased usability, simplified reporting, and streamlined analysis times.

Supporting accurate and efficient microindentation and macroindentation hardness testing in fully automatic, semi-automatic, and lite configurations, the AMH55 is a valuable resource for users needing precise and productive hardness testing while tailoring the data and results to their needs.

The AMH55 is Ideal For:

Case Depth Analysis | Coating Hardness | Surface Analysis
Powdered Metals | Weld Profiles | Fasteners | Decarburization

The AMH55 supports all standard loads for microindentation and macroindentation hardness testing. The AMH55 conforms to ASTM E-384 for micro/macro hardness testing.




User-Friendly Cornerstone Brand Software

LECO's exclusive Cornerstone brand software with touch interface enables the user to have complete access to analysis control, method settings, diagnostics, reporting, and more in a highly organized and immersive environment. Designed through a collaboration of customer feedback and innovative engineering, Cornerstone allows the user to conduct all of their day-to-day operations within a single analysis screen designed for speed and ease of use. Our innovative grouping of sample data into sets and replicates simplifies the data output and automatically calculates relevant statistics, alleviating the need for additional data processing.



Performing a Case Depth Analysis Using the AMH55 Automatic

The AMH55 Automatic Micro/Macro Indentation Hardness Testing System combines the tasks of sample testing, measuring, converting, and documenting into one automated instrument operation. Just load the sample, select the indentation pattern(s), and initiate the test. This fully automated system makes the indentations, measures them, calculates their hardness, and then displays the results.



The AMH55 Semi-Automatic and Lite configurations offer the same great testing capabilities, but with less automatic functionality and features to meet your needs. Both can be upgraded to the fully Automatic version when the time is right.


AMH55 Model Highlights and Features

Choose the model configuration that fits your needs. All models include our exclusive Cornerstone brand software and the following functionality:

- Advanced image-recognition technology allows analysis of information not available with limited threshold-based methods
- Measures impressions with various surface conditions, including scratched or lightly etched

AMH55 Automatic

- Simultaneous automatic alignment and automatic parfocal tools
- Automatic pixel calibration
- Automatic shading correction
- Standard touch-screen interface with multi-touch capabilities
- Streamlined and simplified data reporting; customized spreadsheet generation tools
- Optional Advanced Analysis Module for color contoured mapping




AMH55 Semi-Automatic

- Automatically locates and analyzes indents
- Automatic alignment
- Automatic pixel calibration
- Standard touch-screen interface with multi-touch capabilities
- Customizable data reporting
- Manual Focus
- Upgrade path to AMH55 Automatic available

AMH55 Lite

- Automatically locates and analyzes indents within field of view
- Automatic pixel calibration
- Standard PC/monitor with keyboard and mouse interaction; optional touch-screen interface also available
- Customizable data reporting
- Upgrade path to AMH55 Automatic or Semi-Automatic available



Hardness Tester Options

The AMH55 supports all standard loads for microindentation and macroindentation hardness testing.

LM-Series performs microindentations from 5 gf to 2000 gf with Vickers, Knoop, or dual indenters



LM-810AT



LM-110AT



LM-310AT



LM-248AT



LM-110



LM-810AT

LV-Series performs microindentations from 1 Kg to 50 Kg or 0.3 Kg to 30 Kg with Vickers, Knoop, or dual indenters

Package Configurations

Select one of the following hardness tester options with your AMH55 package.


LM110/310 Series Microindentation
(refer to spec sheet 209-094-001)

LM248/810 Series Microindentation
(refer to spec sheet 209-094-009)

LV110/810 Series Vickers
(refer to spec sheet 209-094-002)

Optional Advanced Analysis Modules

- Color Hardness/Contour Map (shown below)
- Auto Indent Placement
- Auto Case Depth



Optional Color Hardness Contour Map displays sample hardness and location with a color representation of hardness variances.

Options and Accessories

Stage Sample Holders



Anti-Vibration Table



LECO Optical Service

Routine maintenance extends the life of your optical equipment.



Service

Available at our state-of-the-art facility in St. Joseph, Michigan.

Repair

Complete repair and overhaul of your optical equipment by factory trained service specialists.

Calibrations

Calibrations are A2LA accredited in the U.S.A.
(certificate #1845.01; copies available at www.leco.com or call 269-982-2385).

Technical Support

Call LECO Optical Service if you have any questions or problems (269-982-2385).



LECO and Cornerstone are registered trademarks of LECO Corporation.
Microsoft, Excel, are registered trademarks of Microsoft Corporation.

Our global network of sales/support includes over 25 subsidiaries worldwide, and is dedicated to customer service and satisfaction. The one thing all laboratories need to be successful is results they feel confident in. Since 1936, LECO has worked with our customers to find the right solution for the type of sample analysis they are performing, helping them to achieve data that is clear, consistent, and accurate. But our commitment to the customer doesn't end when our instruments are delivered.



LECO Headquarters



Robert J Warren Customer Experience Center



Technical Research Center



Global Support Center

LECO is dedicated to enhancing the user experience long after the sale by offering thorough training on our instruments and technology, accessibility to instrument service programs that keep your instruments in top working order, and access to friendly service and support to ensure you are getting the most out of your purchase—support that will empower your laboratory for success.

LECO, Cornerstone are registered trademarks of LECO Corporation.

3000 Lakeview Avenue | St. Joseph, MI 49085 | 800-292-6141 | Phone: 269-985-5496
info@leco.com | www.leco.com | ISO-9001:2015 Q-994 | LECO is a registered trademark of LECO Corporation.

LECO Corporation

LECO

EMPOWERING RESULTS

© 2022 LECO Corporation